

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2174812224

Status:


Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Mini-Fit Sr. Female-to-Pigtail, Gold (Au) Plating, 300.00mm Length, 8 AWG, Red



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	217481
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mini-Fit Sr. Crimp Terminals
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Mini-Fit Sr.
Taxonomy	Power and Signal Cable Assembl
UPC	195842122444
Physical	
Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	33.159/g
Number of Rows	1
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	6.60mm max.
Wire Size AWG	8
Wire/Cable Type	UL 10669
Electrical	
Current - Maximum per Contact	50.0A
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2174811222-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)10043-DC (17 Jan 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

217481 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION