

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0194180021

Status:

Active

Overview:

MX150L Industrial Sealed Connector System

Description:

MX150L 6 Circuit Receptacle for 14-16 AWG Wire, without CPA, Black



Documents:	
3D Model	Application Specification AS-19417-001-001 (PDF)
3D Model (PDF)	Packaging Specification PK-19418-001-001 (PDF)
Drawing (PDF)	Brochure (PDF)
Product Specification PS-19417-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E152602

General	
Product Family	Crimp Housings
Series	19418
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	IP67 rated; Conforms to UL 1977; NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	MX150L Industrial Sealed Connector System
Product Name	MX150L
Taxonomy	Connector Housings
UPC	822348005970

Physical	
Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Net Weight	17.667/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Electrical	
Current - Maximum per Contact	18.0A

Material Info	
Reference - Drawing Numbers	
Application Specification	AS-19417-001-001
Packaging Specification	PK-19418-001-001
Product Specification	PS-19417-001-001
Sales Drawing	SD-19418-004-001

EU ELV	
Not Relevant	

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19418 Series

Mates With

19419 Plug, 19429 Panel Mount Plug

Use With

19420 Female Crimp Terminal

This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION