

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0734154670](#)
Status: **Active**
Overview: SSMCX Coaxial RF Connectors
Description: 50 Ohms, SSMCX Jack, Edge Mount, Tray

General	
Product Family	RF/Coax Connectors
Series	73415
Overview	<u>SSMCX Coaxial RF Connectors</u>
Product Name	SSMCX
Style	PCB
Taxonomy	RF / Coaxial Connectors
Type	Ultra-microminiature
UPC	822348896912
Wire/Cable Type	N/A

Physical	
Gender	Jack
Keying to Mating Part	None
Net Weight	0.257/g
Orientation	Straight
PCB Mounting	Edge Mount
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
Reverse Polar	No

Electrical	
Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers	
Packaging Specification	895420040-000
Sales Drawing	SD-73415-467-001

EU ELV
Not Relevant

EU RoHS **China RoHS**

Compliant with
Exemption 6(c)
REACH SVHC
Contained Per -
D(2022)4187-DC (10
June 2022)
Lead

Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[73415](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION