

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0194330001

Status:

Active

Overview:

MX150L Industrial Sealed Connector System

Description:

MX150L 4 Circuit Plug for 10-12 AWG Wire



Documents:	
3D Model	Packaging Specification PK-19433-001-001 (PDF)
Drawing (PDF)	Brochure (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19432-001-001 (PDF)	

Agency Certification	
CSA	LR18689
UL	E152602
General	
Product Family	Crimp Housings
Series	19433
Application	Power, Wire-to-Wire
Comments	Mat Seal Color is Yellow, Polarized to Mating Part; IP67 rated; Conforms to UL 1977; NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	MX150L Industrial Sealed Connector System
Product Name	MX150L
Taxonomy	Connector Housings
UPC	822350191579
Physical	
Circuits (maximum)	4
Circuits Detail	2x2
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Net Weight	19.006/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	30.0A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-19433-001-001
Product Specification	PS-19432-001-001
Sales Drawing	SD-19433-002-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19433 Series

Mates With

194320001 Female Receptacle

Use With

19431 Male Terminal

This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION