

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0194290045

Status:

Active

Overview:

MX150L Industrial Sealed Connector System

Description:

MX150L 8 Circuit Panel Mount Plug for 14-22 AWG Wire, Through Hole Flange Assembly, with Gasket, Black



Series image - Reference only

- Documents:
- 3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-19417-001-001 (PDF)

Packaging Specification PK-19429-001-001 (PDF)

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152602
General	
Product Family	Crimp Housings
Series	19429
Application	Power, Wire-to-Wire
Comments	For Outside or Inside Panel Mount Application; IP67 rated; Conforms to UL 1977; NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	MX150L Industrial Sealed Connector System
Product Name	MX150L
Taxonomy	Connector Housings
UPC	822348615131
Physical	
Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Net Weight	15.206/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	18.0A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-19429-001-001
Product Specification	PS-19417-001-001
Sales Drawing	SD-19429-013-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Not Relevant

Not Relevant

Not Contained

Search Parts in this Series

19429 Series

Mates With

19418 MX150L Receptacle Assemblies

Use With

19417 MX150L Male Crimp Terminals

This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION