

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2144151001](#)
Status: **Active**
Overview: [Internet of Things \(IoT\) Antennas: Wi-Fi, Bluetooth, Zigbee](#)
Description: 2.4GHz Wi-Fi/Bluetooth Hinged External Antenna, with SMA Male Connector, White

Documents:
[3D Model](#) [Application Specification 2144150001-AS \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification 2128600001-PK1 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification 2144150001-PS \(PDF\)](#)

General
Product Family Antennas
Series [214415](#)
Component Type External Antenna
Function Signal
Overview [Internet of Things \(IoT\) Antennas: Wi-Fi, Bluetooth, Zigbee](#)
Product Name 2.4GHz Wi-Fi/BT Antenna
Protocol BT, Wi-Fi
Taxonomy Antennas
Type External Antenna
UPC 193264434749

Physical
Length 108.40mm
Mounting Style N/A
Net Weight 7.715/g
Packaging Type PET Bag
Polarization Linear
Radiation Pattern Omnidirectional
Width 9.35mm

Electrical
Band#1 F_End (MHz) 2500
Band#1 F_Start (MHz) 2400
Electrical Connectivity Cable
Peak Gain (dBi) 5.3 @ 2.4 GHz
Return Loss - S11 (dB) < -10
Total Efficiency >80% @ 2.4 GHz

Material Info

Reference - Drawing Numbers
Application Specification 2144150001-AS
Packaging Specification 2128600001-PK1
Product Specification 2144150001-PS
Sales Drawing 2144150001-SD



EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)9139-DC (19 Jan 2021)	
Lead	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[214415](#) Series

Mates With
SMA Female Receptacle