

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0734154223

Status:

Active

Overview:

MCX RF Connectors

Description:

50 Ohms, MCX Jack, Straight, PCB, Gold (Au), 3.94mm Standoff Height

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	RF/Coax Connectors
Series	73415
Overview	MCX RF Connectors
Product Name	MCX
Style	PCB
Taxonomy	RF / Coaxial Connectors
Type	Microminiature
UPC	822350669504
Wire/Cable Type	N/A

Physical	
Gender	Jack
Keying to Mating Part	None
Net Weight	0.586/g
Orientation	Straight
PCB Mounting	Through Hole
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
Reverse Polar	No

Electrical	
Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers	
Sales Drawing	SD-73415-422-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

73415 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION