This document was generated on 02/02/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0391002008
Status: Active
Overview: Eurostyle Two-Screw Barrier Strips
Description: 10.00mm Pitch Beau Eurostyle Two-Screw Terminal Strips, 8 Circuits

Documents:
Drawing (PDF)
RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family	Terminal Blocks
Series	39100
Application	Wire-to-Wire
Component Type	One Piece
Overview	Eurostyle Two-Screw Barrier Strips
Product Name	Eurostyle Two Screw
Taxonomy	Terminal Blocks and Barrier St
Type	Barrier Strip
UPC	78172545157

Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	White
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Stainless Steel
Material - Resin	Nylon
Net Weight	24.000/g
Number of Rows	2
Orientation	Vertical
PCB Retention	Yes
Panel Mount	Mounting Holes Between Circuit
Pitch - Mating Interface	10.00mm
Pitch - Termination Interface	10.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	10, 12, 14, 16, 18

Electrical

Current - Maximum per Contact	30.0A
Voltage - Maximum	600V

Material Info

Engineering Number	M800-02-08-5-M1

Reference - Drawing Numbers

Sales Drawing	SD-39100-013-001

EU ELV
Not Relevant

EU RoHS
Compliant with Exemption 6(c)

China RoHS

REACH SVHC
Contained Per - D(2022)4187-DC (10 June 2022)
Lead

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
39100 Series

This document was generated on 02/02/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION