

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1601116006

Status:

Active

Overview:

MX150 Connector System

Description:

MX150 Hybrid Mat-Sealed Female Connector Assembly, Dual Row, 12 Circuits, Keying Option A, with Connector Position Assurance, Black



Series image - Reference only

- Documents:
- 3D Model

Packaging Specification 1601118002-000 (PDF)
- Drawing (PDF)

Packaging Specification 1601119000-000 (PDF)
- 3D Model (PDF)

Datasheet (PDF)
- Packaging Specification 1601118000-000 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	160111
Application	Power, Wire-to-Wire
Comments	with Connector Position Assurance (CPA)
Overview	MX150 Connector System
Product Name	MX150
Taxonomy	Connector Housings
UPC	889056821681

Physical	
Circuits (maximum)	12
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	20.104/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Material Info

Reference - Drawing Numbers

Packaging Specification	1601118000-000, 1601118002-000, 1601119000-000
Sales Drawing	PK-31300-903-001

EU ELV
Compliant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free
Status
Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
160111 Series

Mates With
MX150 Hybrid Sealed Male Connector
Assembly 160112

Use With
MX150 Female Terminal 33012 , 33001

Industry Standard Terminal 2.80mm

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION