

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2174831212

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Mini-Fit Sr. Male-to-Pigtail, Gold (Au) Plating, 150.00mm Length, 10 AWG, Black

Documents:

Drawing (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Assembly Configuration

Connector to Connector

Overview

Product Name

Taxonomy

UPC

Cable Assemblies

217483

Power, Wire-to-Wire

Pre-crimped Lead Only

Mini-Fit Sr. Crimp Terminals

Off-the-Shelf Pre-Crimped Leads

Mini-Fit Sr.

Power and Signal Cable Assembl

195842122581

Physical

Cable Length

Circuits (Loaded)

Color - Resin

Gender

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Packaging Type

Plating min - Mating

Plating min - Termination

Single Ended

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire/Cable Type

150.00mm

1

Black

Male-Pigtail

Yes

High Performance Alloy (HPA)

Gold

Tin

PVC

12.129/g

1

Bag

0.762µm

2.540µm

Yes

Crimp or Compression

6.60mm max.

10

UL 10669

Electrical

Current - Maximum per Contact

33.0A

Material Info

Reference - Drawing Numbers

Sales Drawing

2174831212-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

217483 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION