

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2042200010

Status:

Active

Overview:

Squba Sealed Wire-to-Wire Connectors

Description:

Squba Sealed Receptacle Assembly, 1.80mm Pitch, 10 Circuits, Single Row, No Seal Plugs

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	204220
Application	Power, Signal, Wire-to-Wire
Overview	Squba Sealed Wire-to-Wire Connectors
Product Name	Squba
Taxonomy	Connector Housings
UPC	191128320306
Physical	
Circuits (maximum)	10
Circuits Detail	No Seal Plugs
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.670/g
Number of Rows	1
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	2042200000-AS-000
Packaging Specification	2042200000-PK-000
Product Specification	2042200000-PS-000, 2042200000-TS-000
Sales Drawing	2042200000-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

204220 Series

Mates With

Squba Sealed Plug Assembly 204223

Squba Sealed Plug Cable Assembly 45146

Use With

Squba Female Terminal 2043010001

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION