

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0369220303](#)
Status: **Active**
Overview: [Ditto Wire-to-Wire Interconnects](#)
Description: Ditto-to-Ditto Off-the-Shelf (OTS) Cable Assembly, 3.00mm Pitch, Single Row, 300.00mm Length, 3 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family Cable Assemblies
Series [36922](#)
Application Power, Wire-to-Wire
Assembly Configuration Dual Ended Connectors
Connector to Connector Ditto-to-Ditto
Overmolded No
Overview [Ditto Wire-to-Wire Interconnects](#)
Product Name Ditto
Taxonomy Power and Signal Cable Assembl
Type Discrete Wire Assembly
UPC 193264208838

Physical

Cable Length 300.00mm
Circuits (Loaded) 3
Color - Resin Black
Gender Hermaphroditic-Hermaphroditic
Lock to Mating Part Yes
Material - Metal Tin Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 11.960/g
Number of Rows 1
Packaging Type Bag
Pitch - Mating Interface 3.00mm
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.35-1.70mm
Wire Size AWG 20
Wire/Cable Type UL 1061

Electrical

Current - Maximum per Contact 4.8A
Voltage - Maximum 300V AC/DC

Material Info

Reference - Drawing Numbers

Sales Drawing 369220300-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[36922](#) Series

Mates With

Ditto Hermaphroditic Crimp Housing [150170](#)