

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982660193](#)
Status: **Active**
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 152.00mm Cable Length, Tin (Sn) Plating, 18 Circuits

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification PS-98266-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-------------------------|---|
| Product Family | Cable |
| Series | 98266 |
| Comments | Contacts on the same side, Type A |
| Crimp Quality Equipment | Yes |
| Overview | FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers |
| Product Name | Premo-Flex FFC Jumper |
| Taxonomy | Flexible Printed Circuit (FPC) |
| UPC | 756054771402 |

Physical

| | |
|-------------------------------|-----------------|
| Cable Length | 152.00mm |
| Circuits (Loaded) | 18 |
| Contact Layout Type | A (same side) |
| Material - Plating Mating | Tin |
| Net Weight | 0.892/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 0.50mm |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | Flat Flex Cable |

Electrical

| | |
|-------------------------------|--------|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum | 60V AC |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|------------------|
| Product Specification | PS-98266-001-001 |
| Sales Drawing | 982660001-000 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[98266 Series](#)

Mates With

Easy-On FFC/FPC Connector:

[527451833](#) , [527461833](#) , [525591834](#)