


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0309681247](#)
Status: **Active**
Overview: H-DAC 64 Unsealed Connector System
Description: 2.54mm Pitch, 0.64mm Width H-DAC 64 Hybrid Male High Density Automotive Crimp Housing, Dual Row, 24 Circuits, Polarization Option A, Gray

Documents:

3D Model	Product Specification PS-30968-024-001 (PDF)
Drawing (PDF)	Packaging Specification PK-30907-760-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Housings
Series	30968
Application	Automotive, Power, Wire-to-Wire
Comments	Polarization Option A
Overview	H-DAC 64 Unsealed Connector System
Polarization	A
Product Name	H-DAC 64
Taxonomy	Connector Housings
UPC	822348858958

Physical

Circuits (maximum)	24
Color - Resin	Gray
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene
Net Weight	16.432/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +100°C

Electrical

Current - Maximum per Contact	7.0A
-------------------------------	------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-30907-760-001
Product Specification	PS-30968-024-001
Sales Drawing	SD-30968-124-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[30968](#) Series

Mates With

[30700](#) , [31389](#) H-DAC 64 High Density Automotive Connectors

Use With

Contact Molex for Terminal information.