

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640074

Status:

Active

Overview:

[Splices](#)

Description:

Perma-Seal 3-Way Connector Assembly for 10-12 AWG Wire

Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-19902-011-001 \(PDF\)](#)

[Product Specification PS-19902-013-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family

Series

Crimp Quality Equipment

Overview

Product Name

Taxonomy

UPC

Splices

19164

Yes

[Splices](#)

3 Way, Perma-Seal

Splices

800753113589

Physical

Barrel Type

Color - Resin

Insulation

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Temperature Range - Operating

Wire Insulation Diameter

Wire Size AWG

Closed

Yellow

NiAc

Copper

Tin

Tin

6.344/g

Bag

2.540µm

2.540µm

-55° to +125°C

7.87mm max.

10, 12

Electrical

Voltage - Maximum

600V

Material Info

Engineering Number

SC-2YCX

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011-001, PS-19902-013-001

SD-19164-051-001, SD-19204-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19164 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

| Global                                                                     |                           |
|----------------------------------------------------------------------------|---------------------------|
| Description                                                                | Product #                 |
| PremiumGrade                                                               | <a href="#">640017400</a> |
| Hand Crimp Tool for Industrial Terminals, 10-22 AWG (see ATS)              |                           |
| Power Crimp Tool                                                           | <a href="#">640057400</a> |
| Head for Terminals 10-22 AWG Wire                                          |                           |
| ServiceGrade Hand                                                          | <a href="#">640160041</a> |
| Crimp Tool for Field Repair only, for production use our PremiumGrade Tool |                           |

This document was generated on 02/01/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**