This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0393570008
Status: Active
Overview: Eurostyle Terminal Blocks
Description: 3.50mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, 8 Circuits



Series image - Reference only

Documents:

- 3D Model
- 3D Model (PDF)
- Drawing (PDF)
- RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E48521

General

Product Family	Terminal Blocks
Series	39357
Application	N/A
Component Type	One Piece
Overview	Eurostyle Terminal Blocks
Product Name	Eurostyle Fixed Mount
Taxonomy	Terminal Blocks and Barrier St
Type	Euro Block
UPC	756054634189

Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Entry Angle	Horizontal
Flammability	94V-0
Lock to Mating Part	None
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	No
Shrouded	Fully
Stackable	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-30° to +85°C
Wire Size AWG	16, 18, 20, 22, 24, 26, 28
Wire Size mm²	0.20-1.00

Electrical

Current - Maximum per Contact	17.5A
Voltage - Maximum	300V

Solder Process Data

Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	005
Process Temperature max. C	260

Material Info

Engineering Number	MX-MTB08008-0N

Reference - Drawing Numbers

EU ELV
Not Relevant

EU RoHS
Compliant with Exemption 6(c)

China RoHS

REACH SVHC
Contained Per - D(2022)4187-DC (10 June 2022)
Lead

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
39357 Series

This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION