

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731120091

Status:

Active

Overview:

FCT D-Sub Connectors

Description:

FCT High Power Contact, Male, Straight, Crimp, 0.20µm Gold Plating, 16-20 AWG

Documents:

Drawing (PDF)

Application Specification 2195600660-000 (PDF)

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Contact Type

Overview

Product Category

Product Name

Taxonomy

Type

UPC

D-Sub Products

173112

High Power

FCT D-Sub Connectors

Contacts

FCT Products

D-Sub Contacts

Mixed Layout

889056331234

Physical

Durability (mating cycles max)

Gender

Material - Contact

Material - Retaining Clip

Net Weight

Orientation

Packaging Type

Plating - Contact

Plating min - Mating

Plating min - Termination

Temperature Range - Operating

Termination Style

Wire Size AWG

200

Male

Copper Alloy

Copper Alloy

2.000/g

Straight

Bag

Gold over Nickel

0.200µm

0.200µm

-55° to +155°C

Crimp

16, 18, 20

Electrical

Current - Maximum per Contact

10.0A

Material Info

Engineering Number

FMP002P106

Reference - Drawing Numbers

Application Specification

Sales Drawing

2195600660-000

1727040142-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

173112 Series

Use With

FCT Mixed Layout Connectors

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION