
This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0395240004
Status: Active
Overview: Eurostyle Terminal Blocks
Description: 5.00mm Pitch Eurostyle Horizontal Plug, with Retention Screws, 4 Circuits



Series image - Reference only

Documents:

3D Model
3D Model (PDF)
Drawing (PDF)
Product Specification PS-39500-001-001 (PDF)
RoHS Certificate of Compliance (PDF)

General	
Product Family	Terminal Blocks
Series	39524
Application	N/A
Component Type	Plug
Overview	Eurostyle Terminal Blocks
Product Name	ESE, Eurostyle Pluggable
Taxonomy	Terminal Blocks and Barrier St
Type	Euro Block
UPC	822350477925
Physical	
Circuits (Loaded)	4
Entry Angle	Vertical
Lock to Mating Part	Yes
Net Weight	9.100/g
Number of Rows	1
Orientation	Horizontal
Panel Mount	No
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	12, 14, 16, 18, 20, 22, 24, 26
Wire Size mm²	0.13-3.31
Electrical	
Current - Maximum per Contact	18.0A
Voltage - Maximum	300V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-39500-001-001
Sales Drawing	SD-39524-001-001, SD-39524-001-002

EU ELV
Not Relevant

EU RoHS
Compliant with Exemption 6(c)

China RoHS

REACH SVHC
Contained Per - D(2022)4187-DC (10 June 2022)
Lead

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
39524 Series

Mates With
Most 5.00mm Pitch Industry Standard PCB Headers, 39525 Vertical PCB Header with Threaded Retention Inserts, 39526 Horizontal PCB Header with Threaded Retention Inserts

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION