

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0369220201](#)
Status: **Active**
Overview: [Ditto Wire-to-Wire Interconnects](#)
Description: Ditto-to-Ditto Off-the-Shelf (OTS) Cable Assembly, 3.00mm Pitch, Single Row, 100.00mm Length, 2 Circuits, Black

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General
Product Family Cable Assemblies
Series [36922](#)
Application Power, Wire-to-Wire
Assembly Configuration Dual Ended Connectors
Connector to Connector Ditto-to-Ditto
Overmolded No
Overview [Ditto Wire-to-Wire Interconnects](#)
Product Name Ditto
Taxonomy Power and Signal Cable Assembl
Type Discrete Wire Assembly
UPC 193264208654

Physical
Cable Length 100.00mm
Circuits (Loaded) 2
Color - Resin Black
Gender Hermaphroditic-Hermaphroditic
Lock to Mating Part Yes
Material - Metal Tin Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 4.039/g
Number of Rows 1
Packaging Type Bag
Pitch - Mating Interface 3.00mm
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.35-1.70mm
Wire Size AWG 20
Wire/Cable Type UL 1061

Electrical
Current - Maximum per Contact 5.0A
Voltage - Maximum 300V AC/DC

Material Info

Reference - Drawing Numbers
Sales Drawing 369220200-000



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2022)4187-DC (10
June 2022)
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[36922](#) Series

Mates With
Ditto Hermaphroditic Crimp Housing [150170](#)