

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2077780003

Status:

Active

Overview:

Squba Sealed Wire-to-Wire Connectors

Description:

Squba 3.6 Sealed Plug Assembly, 3.60mm Pitch, 3 Circuits, Single Row, Glow-Wire Capable



- Documents:
- 3D Model

Packaging Specification 2077780000-PK-000 (PDF)
- Drawing (PDF)

Test Summary 2077760000-TS-000 (PDF)
- 3D Model (PDF)

Datasheet (PDF)
- Product Specification 2077760000-PS-000 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification 2077760000-AS-000 (PDF)

General	
Product Family	Crimp Housings
Series	207778
Application	Power, Signal, Wire-to-Wire
Overview	Squba Sealed Wire-to-Wire Connectors
Product Name	Squba
Taxonomy	Connector Housings
UPC	191130533497
Physical	
Circuits (maximum)	3
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.898/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.60mm
Pitch - Termination Interface	3.60mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Material Info	
Reference - Drawing Numbers	
Application Specification	2077760000-AS-000
Packaging Specification	2077780000-PK-000
Product Specification	2077760000-PS-000
Sales Drawing	2077780000-SD-000
Test Summary	2077760000-TS-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207778 Series

Mates With

Squba 3.6 Receptacle Assembly

2077820003

Use With

Squba 3.6 Crimp Terminal 207776

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION