

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0879331219

Status:

Active

Overview:

Slim-Grid Board-to-Board Connectors

Description:

Slim-Grid Header, 12 Circuits, Surface Mount, Vertical, Unshrouded, 0.05µm Overall Gold (Au) Plated, with Pick-and-Place Cap, Tube, Lead-Free

Documents:

- [Drawing \(PDF\)](#)[Product Specification 879330001-000 \(PDF\)](#)[Packaging Specification PK-89990-565-000 \(PDF\)](#)
- [Datasheet \(PDF\)](#)[RoHS Certificate of Compliance \(PDF\)](#)

General


Product Family	PCB Headers
Series	87933
Application	Board-to-Board, Signal
Comments	4.3 Amps per Pole with only 1 contact powered up; 1.4 Amps per Pole with max contacts powered up
Component Type	PCB Header
Overview	Slim-Grid Board-to-Board Connectors
Product Name	Slim-Grid
Taxonomy	Board-to-Board Connectors
UPC	191128087780

Physical

Breakaway	Yes
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	500
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	0.204/g
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Tube
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.051µm
Plating min - Termination	0.051µm
Polarized to Mating Part	No
Polarized to PCB	No
Robotic Placement	Pick and Place Cap
Shrouded	No
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.4A
-------------------------------	------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[87933](#) Series

Mates With

Slim-Grid Receptacle (Gold Plated) [78120](#)

Voltage - Maximum	125V AC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	011
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-89990-565-000
Product Specification	879330001-000
Sales Drawing	SD-87933-0001-000

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION