This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0395040006
Status: Active
Overview: Eurostyle Terminal Blocks
Description: 3.50mm Pitch Eurostyle Horizontal Plug, with Retention Screws, 6 Circuits

Documents:
Drawing (PDF)
3D Model
3D Model (PDF)
Product Specification PS-39500-001-001 (PDF)
RoHS Certificate of Compliance (PDF)



Series image - Reference only

Agency Certification

UL	E48521

General

Product Family	Terminal Blocks
Series	39504
Application	N/A
Component Type	Plug
Overview	Eurostyle Terminal Blocks
Product Name	ESE, Eurostyle Pluggable
Taxonomy	Terminal Blocks and Barrier St
Type	Euro Block
UPC	822350440073

Physical

Circuits (Loaded)	6
Entry Angle	Vertical
Lock to Mating Part	Yes
Net Weight	4.770/g
Number of Rows	1
Orientation	Horizontal
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm²	0.05-1.31

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V

Material Info

Reference - Drawing Numbers

Product Specification	PS-39500-001-001
Sales Drawing	SD-39504-001-001, SD-39504-001-002

EU ELV
Not Relevant

EU RoHS
Compliant with Exemption 6(c)

China RoHS

REACH SVHC
Contained Per - D(2022)4187-DC (10 June 2022)
Lead

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
39504 Series

Mates With
Most 3.50mm Pitch Industry Standard PCB Headers, 39505 Vertical PCB Header with Threaded Retention Inserts, 39506 Horizontal PCB Header with Threaded Retention Inserts

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION