

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640081

Status:

Active

Overview:

Perma-Seal Terminals

Description:

Perma-Seal Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6)

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19164
Crimp Quality Equipment	Yes
Overview	Perma-Seal Terminals
Product Name	Perma-Seal
Taxonomy	Ring and Spade Terminals
Type	Ring
UPC	800753113657
Physical	
Barrel Type	Closed
Insulation	NiAc
Material - Plating Mating	Tin
Net Weight	4.492/g
Packaging Type	Bag
Stud Size	1/4" (M6)
Wire Insulation Diameter	9.53mm
Wire Size AWG	8
Wire Size mm²	7.96
Material Info	
Engineering Number	SD-651-14
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19164-023-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Not Relevant

REACH SVHC

Not Contained Per - D(2021)10043-DC (17 Jan 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19164 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade HandCrimp Tool for 2-8 AWG Terminals	640013900
Hand Crimp Tool for Perma-Seal Terminals and Butt Splices, 8 AWG	640018200

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION