

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0393800103

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

6.35mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, Modular, 3 Circuits

Documents:

Drawing (PDF)

3D Model (PDF)

3D Model

RoHS Certificate of Compliance (PDF)

General	
Product Family	Terminal Blocks
Series	39380
Application	N/A
Component Type	One Piece
Overview	Eurostyle Terminal Blocks
Product Name	Eurostyle Fixed Mount
Taxonomy	Terminal Blocks and Barrier St
Type	Euro Block
UPC	822348022984
Physical	
Circuits (Loaded)	3
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Resin	Nylon
Number of Rows	1
Orientation	Vertical
PC Tail Length	12.70mm
PCB Retention	None
PCB Thickness - Recommended	4.00mm
Panel Mount	No
Pitch - Mating Interface	6.35mm
Pitch - Termination Interface	6.35mm
Polarized to Mating Part	N/A
Shrouded	Fully
Stackable	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	110°C
Wire Size AWG	10, 12, 14, 16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm²	0.05-5.26
Electrical	
Current - Maximum per Contact	30.0A
Voltage - Maximum	300V
Material Info	
Engineering Number	MX-MSP0300S-0N
Reference - Drawing Numbers	
Sales Drawing	SD-39380-001-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

39380 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION