

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2163012224

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead MX150 Female-to-Pigtail, Gold (Au) Plating, 300.00mm Length, 14 AWG, Red

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Cable Assemblies
Series	216301
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	MX150 Terminal-to-Pigtail
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	MX150
Taxonomy	Power and Signal Cable Assembl
UPC	195842071193
Physical	
Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female-Pigtail
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Net Weight	7.460/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.70mm max.
Wire Size AWG	14
Wire/Cable Type	TXL

Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Material Info

Reference - Drawing Numbers	
Sales Drawing	2163011221-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

216301 Series

Use With

MX150 Dual Row Housing [33472](#) . MX150 Single Row Housing [33471](#) . MX150 Hybrid Housing [33476](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION