
This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0393730006
Status: Active
Overview: Eurostyle Terminal Blocks
Description: 7.50mm Beau Eurostyle Horizontal PCB Header, Closed Ends, 6 Circuits



Series image - Reference only

Documents:

3D Model
3D Model (PDF)
Drawing (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E48521

General

Product Family	Terminal Blocks
Series	39373
Application	N/A
Component Type	PCB Header
Overview	Eurostyle Terminal Blocks
Product Name	Eurostyle Pluggable
Taxonomy	Terminal Blocks and Barrier St
Type	Euro Block
UPC	822348042098

Physical

Circuits (Loaded)	6
Circuits (maximum)	6
Entry Angle	90° Angle
Flammability	94V-0
Lock to Mating Part	None
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.50mm
PCB Retention	None
Panel Mount	No
Pitch - Mating Interface	7.50mm
Pitch - Termination Interface	7.50mm
Polarized to Mating Part	Yes
Shrouded	Closed Ends
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	110°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Material Info

Engineering Number	MX-CIM069P3-0N

Reference - Drawing Numbers

Sales Drawing	SD-39373-001-001

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per - D(2022)4187-DC (10 June 2022)
Halogen-Free Status
Low-Halogen
For more information, please visit Contact US

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
39373 Series

Mates With
39371 , 39374 Plugs

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION