

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0391001803

Status:

Active

Overview:

Eurostyle Two-Screw Barrier Strips

Description:

8.00mm Pitch Beau Eurostyle Two-Screw Terminal Strips, 3 Circuits

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Terminal Blocks

Series

39100

Application

Wire-to-Wire

Component Type

One Piece

Overview

Eurostyle Two-Screw Barrier Strips

Product Name

Eurostyle Two Screw

Taxonomy

Terminal Blocks and Barrier St

Type

Barrier Strip

UPC

78172545121

Physical

Circuits (Loaded)

3

Circuits (maximum)

3

Color - Resin

White

Entry Angle

Horizontal

Lock to Mating Part

None

Material - Metal

Stainless Steel

Material - Resin

Nylon

Net Weight

8.060/g

Number of Rows

2

Orientation

Vertical

PCB Retention

Yes

Panel Mount

Mounting Holes Between Circuit

Pitch - Mating Interface

8.00mm

Pitch - Termination Interface

8.00mm

Polarized to Mating Part

No

Stackable

No

Temperature Range - Operating

-40° to +105°C

Wire Size AWG

12, 14, 16, 18, 20, 22

Electrical

Current - Maximum per Contact

20.0A

Voltage - Maximum

600V

Material Info

Engineering Number

M800-01-03-5-M1

Reference - Drawing Numbers

Sales Drawing

SD-39100-011-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

39100 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION