This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0389690002

Status: Active

Description: 12.70mm Pitch, Single Row Tri-Barrier Terminal Strip, without Mounting Ends, 2 Circuits



Series image - Reference only

Documents:

3D Model
3D Model (PDF)
Drawing (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E48521

General

Product Family	Terminal Blocks
Series	38969
Application	N/A
Component Type	One Piece
Product Name	TSE
Taxonomy	Terminal Blocks and Barrier St
Type	Barrier Strip
UPC	822350944939

Physical

Circuits (Loaded)	2
Circuits (maximum)	2
Entry Angle	90° Angle
Lock to Mating Part	None
Net Weight	17.000/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	4.00mm
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Panel Mount	No
Pitch - Mating Interface	12.70mm
Pitch - Termination Interface	12.70mm
Polarized to Mating Part	Yes
Shrouded	Tri-Barrier
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +120°C
Wire Size AWG	10, 12, 14, 16, 18, 20, 8

Electrical

Current - Maximum per Contact	50.0A
Voltage - Maximum	600V

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-38969-001-001

EU ELV
Not Relevant

EU RoHS | **China RoHS**
Compliant

REACH SVHC
Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
38969 Series

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION