

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640056

Status:

Active

Overview:

Splices

Description:

Perma-Seal Butt Splice for 10-12 AWG Wire

Documents:	
Drawing (PDF)	Product Specification PS-19902-011-001 (PDF)
3D Model	Product Specification PS-19902-013-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Splices
Series	19164
Crimp Quality Equipment	Yes
Overview	Splices
Product Name	Butt, Perma-Seal
Taxonomy	Splices
UPC	800753113411
Physical	
Barrel Type	Closed
Color - Resin	Yellow
Insulation	NiAc
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	3.173/g
Packaging Type	Bag
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	7.87mm max.
Wire Size AWG	10, 12
Electrical	
Voltage - Maximum	600V
Material Info	
Engineering Number	SC-12-10
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19164-017-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)10043-DC (17 Jan 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19164 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade	640017400
Hand Crimp Tool for Industrial Terminals, 10-22 AWG (see ATS)	
Power Crimp Tool	640057400
Head for Terminals 10-22 AWG Wire	
ServiceGrade Hand	640160041
Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION