

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2153461105

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Squba 3.6 Female-to-Pigtail, Tin (Sn) Plating, 450.00mm Length, 20 AWG, Black



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	215346
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Squba-to-Pigtail
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Squba
Taxonomy	Power and Signal Cable Assembl
UPC	195842349452
Physical	
Cable Length	450.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Resin	Modified Polystyrene
Net Weight	2.824/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	3.60mm
Plating min - Mating	2.540µm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.90mm-2.40mm
Wire Size AWG	20
Wire/Cable Type	UL 11028
Electrical	
Current - Maximum per Contact	9.0A
Voltage - Maximum	600V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2153461101-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

215346 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION