

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2153482105

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Squba 3.6 Male-to-Pigtail, Tin (Sn) Plating, 450.00mm Length, 20 AWG, Red



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General

Product Family

Cable Assemblies

Series

215348

Assembly Configuration

Pre-crimped Lead Only

Connector to Connector

Squba-to-Pigtail

Overview

Off-the-Shelf Pre-Crimped Leads

Product Name

Squba

Taxonomy

Power and Signal Cable Assembl

UPC

195842350007

Physical

Cable Length

450.00mm

Circuits (Loaded)

1

Color - Resin

Red

Gender

Male-Pigtail

Lock to Mating Part

Yes

Material - Metal

Copper Alloy

Material - Plating Mating

Matte Tin

Material - Resin

Modified Polystyrene

Net Weight

2.820/g

Number of Rows

1

Packaging Type

Bag

Pitch - Mating Interface

3.60mm

Plating min - Mating

2.540µm

Single Ended

Yes

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

1.90mm-2.40mm

Wire Size AWG

20

Wire/Cable Type

UL 11028

Electrical

Current - Maximum per Contact

9.0A

Voltage - Maximum

600V

Material Info

Reference - Drawing Numbers

Sales Drawing

2153481101-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

215348 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION