This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0395021004
Status: Active
Overview: Eurostyle Terminal Blocks
Description: 3.50mm Pitch Eurostyle Horizontal PCB Header, 4 Circuits

Documents:
3D Model
Drawing (PDF)
3D Model (PDF)
Product Specification PS-39500-001-001 (PDF)
RoHS Certificate of Compliance (PDF)



Series image - Reference only

Agency Certification

UL	E48521

General

Product Family	Terminal Blocks
Series	39502
Application	N/A
Component Type	PCB Header
Overview	Eurostyle Terminal Blocks
Product Name	ESE, Eurostyle Pluggable
Taxonomy	Terminal Blocks and Barrier St
Type	Euro Block
UPC	822350434775

Physical

Circuits (Loaded)	4
Entry Angle	N/A
Lock to Mating Part	None
Net Weight	0.900/g
Number of Rows	1
Orientation	Horizontal
PC Tail Length	3.50mm
PCB Thickness - Recommended	2.50mm
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V

Material Info

Reference - Drawing Numbers

Product Specification	PS-39500-001-001
Sales Drawing	SD-39502-001-001

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per - D(2022)4187-DC (10 June 2022)
Halogen-Free Status
Low-Halogen
For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
39502 Series

Mates With
Most 3.50mm Pitch Industry Standard Plugs, 39500 Horizontal Plug, 39503 Vertical Plug

This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION