

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2153411202](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Mini-Fit Jr. Female-to-Pigtail, Gold (Au) Plating, 150.00mm Length, 20 AWG, Black



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General
Product Family Cable Assemblies
Series [215341](#)
Application Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration Pre-crimped Lead Only
Connector to Connector Mini-Fit Jr. Term-to-Pigtail
Overview [Off-the-Shelf Pre-Crimped Leads](#)
Product Name Mini-Fit Jr.
Taxonomy Power and Signal Cable Assembl
UPC 193264559459

Physical
Cable Length 150.00mm
Circuits (Loaded) 1
Color - Resin Black
Gender Female-Pigtail
Material - Metal Brass
Material - Plating Mating Gold
Material - Plating Termination Tin
Net Weight 2.087/g
Packaging Type Bag
Single Ended Yes
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.80-3.10mm
Wire Size AWG 20
Wire/Cable Type UL 1015

Electrical
Current - Maximum per Contact 9.0A
Voltage - Maximum 600V

Material Info

Reference - Drawing Numbers
Sales Drawing 2153411201-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[215341](#) Series

Use With

Mini-Fit Jr. Receptacle Housing [5557](#)

Mini-Fit BMI Slide and Lock Panel
Mount [44516](#)
Mini-Fit BMI Panel Mount
Receptacle Housing
 [42474](#) , [43760](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION