

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2153412212

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Mini-Fit Jr. Female-to-Pigtail, Gold (Au) Plating, 150.00mm Length, 18 AWG, Red



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	215341
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mini-Fit Jr. Term-to-Pigtail
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Mini-Fit Jr.
Taxonomy	Power and Signal Cable Assembl
UPC	193264559800
Physical	
Cable Length	150.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female-Pigtail
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	2.752/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	18
Wire/Cable Type	UL 1015
Electrical	
Current - Maximum per Contact	9.0A
Voltage - Maximum	600V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2153411211-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

215341 Series

Use With

Mini-Fit Jr. Receptacle Housing [5557](#)

Mini-Fit BMI Slide and Lock Panel
Mount [44516](#)
Mini-Fit BMI Panel Mount
Receptacle Housing
 [42474](#) , [43760](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION