

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2153422225](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Mini-Fit Jr. Male-to-Mini-Fit Jr. Male, Gold (Au) Plating, 450.00mm Length, 16 AWG, Red



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General
Product Family Cable Assemblies
Series [215342](#)
Application Power, Wire-to-Wire
Assembly Configuration Pre-crimped Lead Only
Connector to Connector Mini-Fit Jr. Crimp Terminals
Overview [Off-the-Shelf Pre-Crimped Leads](#)
Product Name Mini-Fit Jr.
Taxonomy Power and Signal Cable Assembl
UPC 193264560080

Physical
Cable Length 450.00mm
Circuits (Loaded) 1
Color - Resin Red
Gender Male-Male
Material - Metal Brass
Material - Plating Mating Gold
Material - Plating Termination Tin
Net Weight 10.124/g
Packaging Type Bag
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.80-3.10mm
Wire Size AWG 16
Wire/Cable Type UL 1015

Electrical
Current - Maximum per Contact 9.0A
Voltage - Maximum 600V

Material Info

Reference - Drawing Numbers
Sales Drawing 2153421221-000

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[215342](#) Series

Use With
Mini-Fit Jr. Plug Housing [5559](#)
Mini-Fit BMI Plug Housing [42475](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION