

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2153432212

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Mini-Fit Jr. Male-to-Pigtail, Gold (Au) Plating, 150.00mm Length, 18 AWG, Red

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General

Product Family

Cable Assemblies

Series

215343

Application

Power, Wire-to-Wire

Assembly Configuration

Pre-crimped Lead Only

Connector to Connector

Mini-Fit Jr. Term-to-Pigtail

Overview

Off-the-Shelf Pre-Crimped Leads

Product Name

Mini-Fit Jr.

Taxonomy

Power and Signal Cable Assembl

UPC

193264560707

Physical

Cable Length

150.00mm

Circuits (Loaded)

1

Color - Resin

Red

Gender

Male-Pigtail

Material - Metal

Brass

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Net Weight

2.782/g

Packaging Type

Bag

Single Ended

Yes

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

1.80-3.10mm

Wire Size AWG

18

Wire/Cable Type

UL 1015

Electrical

Current - Maximum per Contact

9.0A

Voltage - Maximum

600V

Material Info

Reference - Drawing Numbers

Sales Drawing

2153431211-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

215343 Series

Use With

Mini-Fit Jr. Plug Housing [5559](#)
Mini-Fit
BMI Plug Housing [42475](#)

This document was generated on 08/27/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION