

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192050006

Status:

Active

Overview:

Splices

Description:

VersaKrimp Parallel Splice for 6 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Splices
Series	19205
Crimp Quality Equipment	Yes
Overview	Splices
Product Name	Parallel, VersaKrimp
Taxonomy	Splices
UPC	800755060850
Physical	
Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	3.338/g
Packaging Type	Bag
Wire Size AWG	6
Material Info	
Engineering Number	E-361
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19205-007-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

Green Image

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19205 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Manual Putt Pump Hydraulic System, Die set required	192860117
Die Set (large) for the HHLS Hydraulic Crimper	192900004
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	192940008
Hydraulic Dieless Crimping Tool	638161700

PremiumGrade Hand640013900
Crimp Tool for 2-8
AWG Terminals
Square “DIN” style 640037770
dies for 6 AWG
Crimp Head for the 640074300
AT-200 Pneumatic
Hand Tool

This document was generated on 02/02/2023
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION