

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2153411101

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Mini-Fit Jr. Female-to-Pigtail, Tin (Sn) Plating, 75.00mm Length, 20 AWG, Black



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

|                                |                                    |
|--------------------------------|------------------------------------|
| General                        |                                    |
| Product Family                 | Cable Assemblies                   |
| Series                         | 215341                             |
| Application                    | Power, Wire-to-Board, Wire-to-Wire |
| Assembly Configuration         | Pre-crimped Lead Only              |
| Connector to Connector         | Mini-Fit Jr. Term-to-Pigtail       |
| Overview                       | Off-the-Shelf Pre-Crimped Leads    |
| Product Name                   | Mini-Fit Jr.                       |
| Taxonomy                       | Power and Signal Cable Assembl     |
| UPC                            | 193264559299                       |
| Physical                       |                                    |
| Cable Length                   | 75.00mm                            |
| Circuits (Loaded)              | 1                                  |
| Color - Resin                  | Black                              |
| Gender                         | Female-Pigtail                     |
| Material - Metal               | Brass                              |
| Material - Plating Mating      | Tin                                |
| Material - Plating Termination | Tin                                |
| Net Weight                     | 1.270/g                            |
| Packaging Type                 | Bag                                |
| Single Ended                   | Yes                                |
| Termination Interface: Style   | Crimp or Compression               |
| Wire Insulation Diameter       | 1.80-3.10mm                        |
| Wire Size AWG                  | 20                                 |
| Wire/Cable Type                | UL 1015                            |
| Electrical                     |                                    |
| Current - Maximum per Contact  | 9.0A                               |
| Voltage - Maximum              | 600V                               |
| Material Info                  |                                    |
| Reference - Drawing Numbers    |                                    |
| Sales Drawing                  | 2153411101-000                     |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

215341 Series

Use With

Mini-Fit Jr. Receptacle Housing [5557](#)  
<br>Mini-Fit BMI Slide and Lock Panel  
Mount [44516](#) <br>Mini-Fit BMI Panel Mount  
Receptacle Housing<br> [42474](#) , [43760](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION