

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2153411114

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Mini-Fit Jr. Female-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Black

Documents:

Drawing (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Assembly Configuration

Connector to Connector

Overview

Product Name

Taxonomy

UPC

Cable Assemblies

215341

Power, Wire-to-Board, Wire-to-Wire

Pre-crimped Lead Only

Mini-Fit Jr. Term-to-Pigtail

Off-the-Shelf Pre-Crimped Leads

Mini-Fit Jr.

Power and Signal Cable Assembl

193264559374

Physical

Cable Length

Circuits (Loaded)

Color - Resin

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Single Ended

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire/Cable Type

300.00mm

1

Black

Female-Pigtail

Brass

Tin

Tin

5.116/g

Bag

Yes

Crimp or Compression

1.80-3.10mm

18

UL 1015

Electrical

Current - Maximum per Contact

Voltage - Maximum

9.0A

600V

Material Info

Reference - Drawing Numbers

Sales Drawing

2153411111-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

215341 Series

Use With

Mini-Fit Jr. Receptacle Housing [5557](#)

<br>Mini-Fit BMI Slide and Lock Panel Mount [44516](#) <br>Mini-Fit BMI Panel Mount Receptacle Housing<br> [42474](#) , [43760](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION