

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2153411124

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Mini-Fit Jr. Female-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 16 AWG, Black

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General

Product Family

Cable Assemblies

Series

215341

Application

Power, Wire-to-Board, Wire-to-Wire

Assembly Configuration

Pre-crimped Lead Only

Connector to Connector

Mini-Fit Jr. Term-to-Pigtail

Overview

Off-the-Shelf Pre-Crimped Leads

Product Name

Mini-Fit Jr.

Taxonomy

Power and Signal Cable Assembl

UPC

193264559428

Physical

Cable Length

300.00mm

Circuits (Loaded)

1

Color - Resin

Black

Gender

Female-Pigtail

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

6.929/g

Packaging Type

Bag

Single Ended

Yes

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

1.80-3.10mm

Wire Size AWG

16

Wire/Cable Type

UL 1015

Electrical

Current - Maximum per Contact

9.0A

Voltage - Maximum

600V

Material Info

Reference - Drawing Numbers

Sales Drawing

2153411121-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

215341 Series

Use With

Mini-Fit Jr. Receptacle Housing [5557](#)

Mini-Fit BMI Slide and Lock Panel Mount [44516](#)
Mini-Fit BMI Panel Mount Receptacle Housing
 [42474](#) , [43760](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION