

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2153421123](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Mini-Fit Jr. Male-to-Mini-Fit Jr. Male, Tin (Sn) Plating, 225.00mm Length, 16 AWG, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family Cable Assemblies
Series [215342](#)
Application Power, Wire-to-Wire
Assembly Configuration Pre-crimped Lead Only
Connector to Connector Mini-Fit Jr. Crimp Terminals
Overview [Off-the-Shelf Pre-Crimped Leads](#)
Product Name Mini-Fit Jr.
Taxonomy Power and Signal Cable Assembl
UPC 193264559916

Physical

Cable Length 225.00mm
Circuits (Loaded) 1
Color - Resin Black
Gender Male-Male
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 5.335/g
Packaging Type Bag
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.80-3.10mm
Wire Size AWG 16
Wire/Cable Type UL 1015

Electrical

Current - Maximum per Contact 9.0A
Voltage - Maximum 600V

Material Info

Reference - Drawing Numbers

Sales Drawing 2153421121-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[215342](#) Series

Use With

Mini-Fit Jr. Plug Housing [5559](#)
Mini-Fit
BMI Plug Housing [42475](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION