

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2157102123

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Clik-Mate Male-to-Clik-Mate Male, Tin (Sn) Plating, 225.00mm Length, 24 AWG, Red



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	215710
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	CLIK-Mate 1.50mm Crimp Term
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	CLIK-Mate
Taxonomy	Power and Signal Cable Assembl
UPC	193264605033
Physical	
Cable Length	225.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Male-Male
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.797/g
Packaging Type	Bag
Plating min - Mating	0.406µm
Plating min - Termination	0.406µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.78-1.28mm
Wire Size AWG	24
Wire/Cable Type	UL 10002
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	100V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2157101121-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

215710 Series

Use With

CLIK-Mate Housing [502578](#) , [503149](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION