

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2157112111](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Clik-Mate Male-to-Pigtail, Tin (Sn) Plating, 75.00mm Length, 26 AWG, Red



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General
Product Family Cable Assemblies
Series [215711](#)
Application Signal, Wire-to-Board
Assembly Configuration Pre-crimped Lead Only
Connector to Connector CLIK-Mate Terminal-to-Pigtail
Overview [Off-the-Shelf Pre-Crimped Leads](#)
Product Name CLIK-Mate
Taxonomy Power and Signal Cable Assembl
UPC 193264605262

Physical
Cable Length 75.00mm
Circuits (Loaded) 1
Color - Resin Red
Gender Male-Pigtail
Material - Metal Copper Alloy
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.221/g
Packaging Type Bag
Plating min - Mating 0.406µm
Plating min - Termination 0.406µm
Single Ended Yes
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 0.78-1.28mm
Wire Size AWG 26
Wire/Cable Type UL 10002

Electrical
Current - Maximum per Contact 2.0A
Voltage - Maximum 100V AC (RMS)/DC

Material Info

Reference - Drawing Numbers
Sales Drawing 2157111111-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[215711](#) Series

Use With

CLIK-Mate Housing [502578](#) , [503149](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION