

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2157112114

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Clik-Mate Male-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 26 AWG, Red

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General

Product Family

Cable Assemblies

Series

215711

Application

Signal, Wire-to-Board

Assembly Configuration

Pre-crimped Lead Only

Connector to Connector

CLIK-Mate Terminal-to-Pigtail

Overview

Off-the-Shelf Pre-Crimped Leads

Product Name

CLIK-Mate

Taxonomy

Power and Signal Cable Assembl

UPC

193264605293

Physical

Cable Length

300.00mm

Circuits (Loaded)

1

Color - Resin

Red

Gender

Male-Pigtail

Material - Metal

Copper Alloy

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

0.714/g

Packaging Type

Bag

Plating min - Mating

0.406µm

Plating min - Termination

0.406µm

Single Ended

Yes

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

0.78-1.28mm

Wire Size AWG

26

Wire/Cable Type

UL 10002

Electrical

Current - Maximum per Contact

2.0A

Voltage - Maximum

100V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing

2157111111-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

215711 Series

Use With

CLIK-Mate Housing 502578 , 503149

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION