

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015311092](#)
Status: **Active**
Description: 4.80mm Pitch Wire-to-Wire Receptacle Housing, 9 Circuits, Natural

Documents:

Drawing (PDF)	Product Specification PS-5025-003-001 (PDF)
Product Specification PS-5025-001-001 (PDF)	Packaging Specification SPK-5025-001-001 (PDF)
Product Specification PS-5025-002-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	5025
Application	Power, Wire-to-Wire
Product Name	N/A
Taxonomy	Connector Housings
UPC	800753604179

Physical

Circuits (maximum)	9
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	3193.400/mg
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	4.80mm
Temperature Range - Operating	-40° to +105°C

Material Info

Engineering Number	5025-09R1
--------------------	-----------

Reference - Drawing Numbers

Packaging Specification	SPK-5025-001-001
Product Specification	PS-5025-001-001, PS-5025-002-001, PS-5025-003-001
Sales Drawing	SD-5025-09R1-001, SD-5025-09R1-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[5025](#) Series

Mates With

[15311091](#) , [15311093](#) Plug

Use With

[5005](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION