

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2153462103

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Squba 3.6 Female-to-Pigtail, Tin (Sn) Plating, 225.00mm Length, 20 AWG, Red

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General

Product Family

Cable Assemblies

Series

215346

Assembly Configuration

Pre-crimped Lead Only

Connector to Connector

Squba-to-Pigtail

Overview

Off-the-Shelf Pre-Crimped Leads

Product Name

Squba

Taxonomy

Power and Signal Cable Assembl

UPC

195842349582

Physical

Cable Length

225.00mm

Circuits (Loaded)

1

Color - Resin

Red

Gender

Female-Pigtail

Lock to Mating Part

Yes

Material - Metal

Copper Alloy

Material - Plating Mating

Matte Tin

Material - Resin

Modified Polystyrene

Net Weight

1.564/g

Number of Rows

1

Packaging Type

Bag

Pitch - Mating Interface

3.60mm

Plating min - Mating

2.540µm

Single Ended

Yes

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

1.90mm-2.40mm

Wire Size AWG

20

Wire/Cable Type

UL 11028

Electrical

Current - Maximum per Contact

9.0A

Voltage - Maximum

600V

Material Info

Reference - Drawing Numbers

Sales Drawing

2153461101-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

215346 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION