

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192160011](#)
Status: **Active**
Description: Ultimate Wire Tap, Red, 18-22 AWG, 0.34 - .075mm²

Documents:

3D Model	Product Specification PS-19902-011-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E79133

General

Product Family	IDT and Solder Connectors
Series	19216
Crimp Quality Equipment	Yes
Product Name	Wire Tap
Taxonomy	Connector Housings
UPC	800753022133

Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Natural
Durability (mating cycles max)	25
Flammability	94V-2
Gender	N/A
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Resin	Nylon
Net Weight	1.130/g
Number of Rows	0
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Pitch - Termination Interface	N/A
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	105°C
Wire Insulation Diameter	N/A
Wire Size AWG	18, 20, 22

Electrical

Voltage - Maximum	600V
-------------------	------

Material Info

Engineering Number	WT-2218
--------------------	---------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19216-008-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19216 Series](#)

Mates With

Male Quick Disconnect

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION