

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0193240016

Status:

Active

Overview:

Metric Ring Terminals

Description:

Avikrimp Metric Ring Terminal for Stud Size M10, Insulated Barrel

Documents:	
3D Model (PDF)	3D Model
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19324
Crimp Quality Equipment	Yes
Overview	Metric Ring Terminals
Product Name	Avikrimp
Taxonomy	Ring and Spade Terminals
Type	Ring
UPC	887191290164
Physical	
Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	2.676/g
Packaging Type	Bag
Stud Size	M10
Wire Size AWG	N/A
Wire Size mm²	2.50-6.00
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	C6-840-M10
Reference - Drawing Numbers	
Sales Drawing	SD-19324-001-001



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series	
19324 Series	
Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades) Crimp Head for the AT-200 Pneumatic Hand Tool	640010100
	640050100

ServiceGrade Hand 640160036
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION