

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0397000702](#)
Status: **Active**
Overview: Eurostyle Terminal Blocks
Description: 3.50mm Pitch, Eurostyle Fixed-Mount Push-Button Terminal Block, 45° Modular, 5A, 20-16 AWG, Light Gray, 2 Circuits

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|----------------|---|
| Product Family | Terminal Blocks |
| Series | 39700 |
| Application | Wire-to-Board |
| Component Type | Push-Button |
| Overview | Eurostyle Terminal Blocks |
| Product Name | ESE, Eurostyle Fixed Mount |
| Taxonomy | Terminal Blocks and Barrier St |
| Type | Euro Block |
| UPC | 78172542532 |

Physical

| | |
|--------------------------------|----------------|
| Circuits (Loaded) | 2 |
| Circuits (maximum) | 2 |
| Color - Resin | Gray (Light) |
| Entry Angle | 45° Angle |
| Lock to Mating Part | No |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 1.070/g |
| Number of Rows | 1 |
| Orientation | 45° Angle |
| Panel Mount | Yes |
| Pitch - Mating Interface | 3.50mm |
| Polarized to Mating Part | No |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | 16, 18, 20 |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 5.0A |
| Voltage - Maximum | 300V |

Solder Process Data


| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

| | |
|--------------------|--------------|
| Engineering Number | M710-02-02-9 |
|--------------------|--------------|

Reference - Drawing Numbers

| | |
|---------------|------------------|
| Sales Drawing | SD-39700-008-001 |
|---------------|------------------|



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[39700 Series](#)