

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0190560089](#)  
**Status:** **Active**  
**Description:** RING VERSAKRIMP (B-330-56HD) SPM

**Documents:**

|                                |  |
|--------------------------------|--|
| <a href="#">3D Model</a>       | <a href="#">Product Specification PS-19902-011-001 (PDF)</a> |
| <a href="#">3D Model (PDF)</a> | <a href="#">Product Specification PS-19902-013-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>  | <a href="#">RoHS Certificate of Compliance (PDF)</a>         |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR18689 |
| UL  | E32244  |

**General**

|                         |                          |
|-------------------------|--------------------------|
| Product Family          | Ring and Spade Terminals |
| Series                  | <a href="#">19056</a>    |
| Crimp Quality Equipment | Yes                      |
| Taxonomy                | Ring and Spade Terminals |
| UPC                     | 800755063509             |

**Physical**

|            |         |
|------------|---------|
| Net Weight | 2.232/g |
|------------|---------|

**Material Info**

|                    |            |
|--------------------|------------|
| Engineering Number | B-330-56HD |
|--------------------|------------|

**Reference - Drawing Numbers**

|                       |                                    |
|-----------------------|------------------------------------|
| Product Specification | PS-19902-011-001, PS-19902-013-001 |
| Sales Drawing         | BHD30101-001                       |

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19056](#) Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

| Description  | Product #                 |
|--|---------------------------|
| PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm <sup>2</sup> - 0.5mm <sup>2</sup> Crimp Head for the AT-200 Pneumatic Hand Tool | <a href="#">640030100</a> |
| ServiceGrade Hand Crimp Tool - Ratchet   | <a href="#">640070100</a> |
|  | <a href="#">640160038</a> |

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**